



LP200 & LP200S

SOLDAVAC Lifter

by Pen Vac Portable Vacuum Pick-up Tool



LP200 with LN250 Lifting Needle



LP200S with LN270S Stealth Lifting Needle

Instruction

To pick-up SMD place lifting needle on a clean surface and press rectangular button and release, this will create a vacuum to hold the device. To release the SMD simply press the rectangular button.

Specifications

Length: 6 inches Diameter: ½ Inch Weight: .025 lbs.
Material: Black Static Dissipative Plastic Body with Conductive Black Silicone Vacuum Cups.

Lifting Needles

Standard Type



Stealth Needles



Suction Cups

Standard Type Enlarged View



Suction cups may be attached directly to the LP200 Body.